


Tooling list for end sleeves for correct crimping according to UL

Insulated end sleeves, tape-mounted, multinorm

(BN 22323, BN 22324, BN 22325)



□ mm ²	L	AWG	Stripping length [mm]	UL Wire class	UL certified machine**
0.5	8	21	12	B, K	
0.5	10	21	14	B, K	
0.75	8	19	12	B, K, Q	
0.75	10	19	14	B, K, Q	
1	8	18	12	B, K, Q	
1	10	18	14	B, K, Q	
1.5	8	16	12	B, K	
1.5	10	16	14	B, K	
2.5*	8	14	12	B, K	
2.5*	10	14	14	B, K	

Certified to UL486F/CSA

* Identical with the standard 2,5mm²-version

** For more information about UL certified machines, please contact our Product Management Electrical elektro@bossard.com